

# CARSON®

## Pop Up Keychain Magnifier™

### 7x Magnification

Congratulations on selecting your new Pop Up Keychain Magnifier! In order to achieve optimum performance, please follow instructions for proper use and care.

#### PRODUCT SPECIFICATION


Magnification:	7x
Weight:	0.2 lbs
Dimensions:	1.1" x 0.3" x 2.3"



## GN-70

#### USING KEYCHAIN MAGNIFIER

1. To open magnifier, push spring-loaded button on bottom left to extend magnifier out (Fig 1).
2. Place magnifier over the object you are viewing.  
**For Best Results:** Depending on your vision, you may need to move the magnifier closer or further away until object is in focus.
3. To close magnifier, gently push top of magnifier down into protective housing (Fig. 2).



#### CARE

Clean using microfiber lens cloth. Do not use any abrasives, chemical cleaners, or solvents.

#### Customer Service:

If you experience any difficulties, please contact us and we will be happy to help you.



✉ [info@carson.com](mailto:info@carson.com)



✉ [uksupport@carson.com](mailto:uksupport@carson.com)



✉ [eusupport@carson.com](mailto:eusupport@carson.com)

For warranty information, visit [www.carson.com/warranty](http://www.carson.com/warranty)

[www.carson.com](http://www.carson.com)

Carson Optical 2070 5th Avenue, Ronkonkoma, NY 11779 | Tel: 631-963-5000